

Insertor/Extractor Handle Type IET, Black Lever, Grey Button, Bottom, 100 Pieces

CATALOG NUMBER

20817-653



The inserter/extractor handle, type IET in accordance with IEEE 1101.10. Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICATIONS



FEATURES

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

Package Quantity: 100
Handle Type: IET; Bottom Front; Top Rear I/O
Flammability Rating: UL® 94V-0
Color: Black
Complies With: EN 45545-2
Material: Polycarbonate; Zinc Alloy
Product Type: Handle
Type: Inserter/Extractor, Standard
Works With: Front Panels
Gross Weight: 2.256kg

Please order Coding pegs and Microswitch separately.

Technical drawing of the 3000 Series Locking Bolt Assembly, showing exploded and assembled views with dimensions.

Exploded View (Top): Shows the assembly of the handle (1), lock body (2), and locking bolt (3). The handle has a width of 4.07. The lock body has a height of 4.5 and a width of 2.5. The locking bolt has a length of 12.75 and a diameter of 2.54.

Exploded View (Bottom): Shows the assembly of the handle (1), lock body (2), and locking bolt (3). The handle has a width of 4.07. The lock body has a height of 4.5 and a width of 2.5. The locking bolt has a length of 12.75 and a diameter of 2.54.

Assembled View (Top): Shows the handle (1) mounted on the lock body (2). The handle has a width of 4.07. The lock body has a height of 4.5 and a width of 2.5. The locking bolt (3) is shown in the assembled position with a length of 12.75 and a diameter of 2.54. The total width of the assembly is 22.75.

Assembled View (Bottom): Shows the handle (1) mounted on the lock body (2). The handle has a width of 4.07. The lock body has a height of 4.5 and a width of 2.5. The locking bolt (3) is shown in the assembled position with a length of 12.75 and a diameter of 2.54. The total width of the assembly is 22.75.

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE