

PropacPRO Portable Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition this case is prepared for the fitting of a tip-up carrying handle, which is part of the extensive accessory range.

CERTIFICATIONS



FEATURES

Desktop case for individual assembly

Prepared with holes for fitting of tip-up carrying handle

Retrofittable EMC shielding

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

Prepared for GND/earthing

Conforms with DIN EN 62368-1

SPECIFICATIONS

Product Type:	Case
Type:	Case for Individual Electronic Components
Product Family:	PropacPRO

Table 1/3

Catalog Number	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
----------------	-------------	------------	-------	------------------	---------------	--------------

14577-123	3U	42HP	326mm	1	130mm	219mm
14577-125	3U	42HP	386mm	1	130mm	219mm
14577-143	3U	63HP	326mm	1	130mm	326mm
14577-145	3U	63HP	386mm	1	130mm	326mm
14577-163	3U	84HP	326mm	1	130mm	432mm
14577-165	3U	84HP	386mm	1	130mm	432mm
14577-223	4U	42HP	326mm	1	174mm	219mm
14577-243	4U	63HP	326mm	1	174mm	326mm
14577-245	4U	63HP	386mm	1	174mm	326mm
14577-265	4U	84HP	386mm	1	174mm	432mm

Table 2/3

Catalog Number	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Height
14577-123	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	155.5mm
14577-125	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	155.5mm
14577-143	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	155.5mm
14577-145	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	155.5mm
14577-163	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	155.5mm
14577-165	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	155.5mm
14577-223	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	200mm

CatalogNumber	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Height
14577-243	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	200mm
14577-245	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	200mm
14577-265	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Powder Coated	200mm

Table 3/3					
Catalog Number	Material	Protection Rating	Static Load	Width	Quick Ship
14577-123	Aluminum	IP20	25kg	257mm	No
14577-125	Aluminum	IP20	25kg	257mm	No
14577-143	Aluminum	IP20	25kg	363.7mm	No
14577-145	Aluminum	IP20	25kg	363.7mm	No
14577-163	Aluminum	IP20	25kg	470.3mm	No
14577-165	Aluminum	IP20	25kg	470.3mm	No
14577-223	Aluminum	IP20	25kg	257mm	No
14577-243	Aluminum	IP20	25kg	363.7mm	No
14577-245	Aluminum	IP20	25kg	363.7mm	No
14577-265	Aluminum	IP20	25kg	470.3mm	No

ADDITIONAL PRODUCT DETAILS

Please order tip up carrying handle separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE