

# Rack Safety Plus, 3 U, 120 V AC



## FEATURES

19", 3 U Power Distribution Unit with Emergency Stop function

Supplies AC mains power to electrical or electronic devices as a central power switch

120 V phase to neutral mains input

AC outputs with different connector types, switched by ON/OFF switch

Permanent AC Outputs (Service)

All outputs are protected by circuit breakers

The emergency stop function meets the requirements of EN 60947-5-1 and EN 60204-1 and is vandalism-proof

An additional external emergency stop push button can be connected to the system

UL pending

## SPECIFICATIONS

|                                 |                                |
|---------------------------------|--------------------------------|
| <b>Function:</b>                | Emergency Stop                 |
| <b>Inrush Current Limiter:</b>  | No                             |
| <b>Residual Current Device:</b> | No                             |
| <b>Circuit Breaker Cover:</b>   | No                             |
| <b>Works With:</b>              | Varistar CP; Novastar          |
| <b>Accessory Type:</b>          | Power distribution accessories |

Table 1/2

| Catalog Number | Product Type      | Input Voltage AC | Number of Phases | EMC Filter | Surge Arrester | Rack Height |
|----------------|-------------------|------------------|------------------|------------|----------------|-------------|
| 21272-002      | Power Distributor | 120V             | 1                | Yes        | Yes            | 3U          |
| 21272-004      | Power Distributor | 120V             | 1                | No         | No             | 3U          |

Table 2/2

| Catalog Number | Socket Type            | Package Quantity | Quick Ship |
|----------------|------------------------|------------------|------------|
| 21272-002      | NEMA 5-15R, NEMA 5-20R | 1                | No         |
| 21272-004      | NEMA 5-15R             | 1                | No         |

## ADDITIONAL PRODUCT DETAILS

For exact configuration of optional features and example configuration please refer to the item(s) delivered table.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**