

# nVent CADDY Rod Lock Spring Steel Rod Hanger with Nail Gun Bracket



## CERTIFICATIONS



## FEATURES

Suspends threaded rod without the need for additional hardware

Complete with concrete nail gun insert bracket

Clips onto nozzle of gas or battery-actuated nail guns allowing for hands-off installation at structure or from the floor using a pole

Longer leg angle bracket for tool clearance

Quickly and easily attaches to concrete, steel or composite metal decking

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Works with slightly damaged threads and minor burrs on threaded rod ends

Design includes a release mechanism that works with pliers

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material                   | Finish                                | Rod Size (RS) | Height (H) | Width (W) |
|----------------|----------------|----------------------------|---------------------------------------|---------------|------------|-----------|
| 4QTIGBSF       | 170896         | Spring Steel, Steel, Nylon | nVent CADDY Armour, Electrogalvanized | 6             | 48.7 mm    | 66.8 mm   |

Table 2/2


| Catalog Number | Article Number | A       | B     | Static Load |
|----------------|----------------|---------|-------|-------------|
| 4QTIGBSF       | 170896         | 46.4 mm | 36 mm | 330N        |

## ADDITIONAL PRODUCT DETAILS

Static Load represents the static load of the nail gun insert assembly. Please consult with the nail manufacturer to evaluate the static load of the nail and type of concrete used for the installation. Maximum load is the lesser of the static load from the nail manufacturer or the published load for the assembly.

Nail gun insert is compatible with BeA® CN60-688ES, Hilti® BX 3, GX 3, DEWALT® Trak-It C3, SPIT® PULSA 40E, 800E, 700, 1000 or equivalent nailers.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

