

Varistar CP Server Cabinet, RAL 7021, With Castors, 42 U, 2000H, 800W, 1200D

Data Solutions

CATALOG NUMBER

10630-022



Welded steel frame for high dynamic load requirements.
Prepared for 19" integration of IT assets.

FEATURES

Preconfigured, ready to use cabinet

High dynamic load 1000 kg with integrated castors, static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

PRODUCT ATTRIBUTES

Rack Height: 42U

Height: 2000mm

Cladding Material: Steel

Width: 800mm

Cladding Color: Black Grey

Depth: 1200mm

Package Quantity: 1

Dynamic Load: 1000kgf

Cladding Color Code: RAL 7021

Finish: Powder Coated

Frame Material: Steel

Material: Steel

Product Family: Varistar CP

Product Type: Rack

Static Load: 1600kg

Type: Mobile

Net Weight: 168.95kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE