

# Cable Entry Gland Plate Connected Locking Inside, CCFLI



Available as an option, CCFL locking frames help ensure grommets stay in place and cannot be removed or pushed out without using tools.

## INDUSTRY STANDARDS

UL 508A Component Recognized; Type 1, 12, 4X (indoor only); File No. E61997

UL94 V-0 Flammability

## FEATURES

Finish: Black

Pack quantity: 10

Description: The locking frames are compatible with CCFO and CCFI cable entry systems. The locking elements help ensure grommets cannot be pushed out without using tools. To maintain UL-certification, CCFLO needs to be used together with CCFO.

Temperature resistance: -40°C to +120°C

Flammability: UL94 V-0

Material: Polyamide 6.6

SPECIFICATIONS

| Table 1/1      |        |       |        |           |           |       |
|----------------|--------|-------|--------|-----------|-----------|-------|
| Catalog Number | Height | Width | Depth  | Material  | Finish    | Color |
| CCFLI14        | 80mm   | 70mm  | 11.5mm | Polyamide | Untreated | Black |
| CCFLI610       | 105mm  | 70mm  | 11.5mm | Polyamide | Untreated | Black |
| CCFLI816       | 125mm  | 70mm  | 11.5mm | Polyamide | Untreated | Black |
| CCFLI1024      | 152mm  | 70mm  | 11.5mm | Polyamide | Untreated | Black |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE