

## Profiles 19-inch, AVP



19" equipment can be easily fitted in wall mounted enclosures, either in the factory or in the field, when these profiles are used.

### FEATURES

---

Description: For 600 mm wide enclosures only. Adjustable depth with the use of the AMG accessory. Usable depth between 19" profiles and external door: 56 mm. Fitted onto the hinge holes located on the front frame of the enclosure. For stainless steel enclosures, machining is required.

Material: 2 mm galvanized steel.

Pack quantity: 1 pair with mounting accessories.

SPECIFICATIONS

**Thickness:** 2mm  
**Finish:** Galvanized  
**Material:** Mild Steel

| Table 1/1      |        |       |       |            |                    |            |
|----------------|--------|-------|-------|------------|--------------------|------------|
| Catalog Number | Height | Width | Depth | Rack Units | Enclosure Material | Quick Ship |
| AVP0600        | 600mm  | 55mm  | 50mm  | 13U        | Mild Steel         | No         |
| AVP1200        | 1200mm | 55mm  | 50mm  | 26U        | Mild Steel         | No         |
| AVP0800        | 800mm  | 55mm  | 50mm  | 17U        | Mild Steel         | No         |
| AVP1000        | 1000mm | 55mm  | 50mm  | 21U        | Mild Steel         | No         |

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE