

# Novastar Cabinet With Glazed Door and Rear Panel



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

## CERTIFICATIONS



## FEATURES

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

## SPECIFICATIONS

|                           |                            |
|---------------------------|----------------------------|
| <b>Frame Material:</b>    | Aluminum                   |
| <b>Material:</b>          | Aluminum; Steel            |
| <b>Product Type:</b>      | Cabinet                    |
| <b>Complies With:</b>     | IEC 60529; IEC 60297-3-100 |
| <b>Protection Rating:</b> | IP20                       |

Table 1/3

| Catalog Number | Rack Height | Frame Color | Height | Frame Color Code | Cladding Material | Width |
|----------------|-------------|-------------|--------|------------------|-------------------|-------|
| 15230-019      | 12U         | Black Grey  | 589mm  | RAL 7021         | Steel             | 553mm |
| 15230-020      | 16U         | Black Grey  | 767mm  | RAL 7021         | Steel             | 553mm |
| 15230-021      | 20U         | Black Grey  | 945mm  | RAL 7021         | Steel             | 553mm |
| 15230-022      | 38U         | Black Grey  | 1745mm | RAL 7021         | Steel             | 553mm |
| 15230-023      | 38U         | Black Grey  | 1745mm | RAL 7021         | Steel             | 553mm |
| 15230-024      | 43U         | Black Grey  | 1967mm | RAL 7021         | Steel             | 553mm |
| 15230-025      | 43U         | Black Grey  | 1967mm | RAL 7021         | Steel             | 553mm |
| 16230-019      | 12U         | Black Grey  | 589mm  | RAL 7021         | Steel             | 553mm |
| 16230-020      | 16U         | Black Grey  | 767mm  | RAL 7021         | Steel             | 553mm |
| 16230-021      | 20U         | Black Grey  | 945mm  | RAL 7021         | Steel             | 553mm |
| 16230-022      | 38U         | Black Grey  | 1745mm | RAL 7021         | Steel             | 553mm |
| 16230-023      | 38U         | Black Grey  | 1745mm | RAL 7021         | Steel             | 553mm |
| 16230-024      | 43U         | Black Grey  | 1967mm | RAL 7021         | Steel             | 553mm |
| 16230-025      | 43U         | Black Grey  | 1967mm | RAL 7021         | Steel             | 553mm |

Table 2/3

| Catalog Number | Cladding Color | Depth | Static Load | Cladding Color Code | Package Quantity | Finish        |
|----------------|----------------|-------|-------------|---------------------|------------------|---------------|
| 15230-019      | Black Grey     | 600mm | 200kg       | RAL 7021            | 1                | Powder Coated |
| 15230-020      | Black Grey     | 600mm | 200kg       | RAL 7021            | 1                | Powder Coated |

| CatalogNumber | Cladding Color | Depth | Static Load | Cladding Color Code | Package Quantity | Finish        |
|---------------|----------------|-------|-------------|---------------------|------------------|---------------|
| 15230-021     | Black Grey     | 600mm | 200kg       | RAL 7021            | 1                | Powder Coated |
| 15230-022     | Black Grey     | 600mm | 400kg       | RAL 7021            | 1                | Powder Coated |
| 15230-023     | Black Grey     | 800mm | 400kg       | RAL 7021            | 1                | Powder Coated |
| 15230-024     | Black Grey     | 600mm | 400kg       | RAL 7021            | 1                | Powder Coated |
| 15230-025     | Black Grey     | 800mm | 400kg       | RAL 7021            | 1                | Powder Coated |
| 16230-019     | Light Grey     | 600mm | 200kg       | RAL 7035            | 1                | Powder Coated |
| 16230-020     | Light Grey     | 600mm | 200kg       | RAL 7035            | 1                | Powder Coated |
| 16230-021     | Light Grey     | 600mm | 200kg       | RAL 7035            | 1                | Powder Coated |
| 16230-022     | Light Grey     | 600mm | 400kg       | RAL 7035            | 1                | Powder Coated |
| 16230-023     | Light Grey     | 800mm | 400kg       | RAL 7035            | 1                | Powder Coated |
| 16230-024     | Light Grey     | 600mm | 400kg       | RAL 7035            | 1                | Powder Coated |
| 16230-025     | Light Grey     | 800mm | 400kg       | RAL 7035            | 1                | Powder Coated |

| Table 3/3      |            |
|----------------|------------|
| Catalog Number | Quick Ship |
| 15230-019      | No         |
| 15230-020      | No         |
| 15230-021      | No         |
| 15230-022      | No         |
| 15230-023      | No         |

| Catalog Number | Quick Ship |
|----------------|------------|
| 15230-024      | No         |
| 15230-025      | No         |
| 16230-019      | No         |
| 16230-020      | No         |
| 16230-021      | No         |
| 16230-022      | No         |
| 16230-023      | No         |
| 16230-024      | No         |
| 16230-025      | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**