


Varistar CP 19" Panel/Slide Mount

Data Solutions



Slide mount with adjustable increments. Assembly in 600 mm wide cabinets directly on the frame. At 800 mm width adapter bracket for reduced width is necessary, for partial-height mounting depth members are necessary.

FEATURES

19" panel/slide mount with U indicator

Depth-adjustable in 25 mm increments

In accordance with IEC 60297-1 (DIN 41 494, Part 1)

SPECIFICATIONS

Finish: Powder Coated

Product Type: Slide Mount

Material: Steel

Table 1/1

Catalog Number	Rack Height	Height	Package Quantity	Color	Color Code
24630-013	42U	2000mm	4	Jet Black	RAL 9005
24630-014	47U	2200mm	4	Jet Black	RAL 9005
24630-015	52U	2450mm	4	Jet Black	RAL 9005

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE