We connect and protect

Varistar CP Steel Door, Perforated With 1-Point Locking

Data Solutions

Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

FEATURES

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

SPECIFICATIONS

Product Type: Cabinet Door

Protection Rating: IP20

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-006	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-007	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-008	52U	2450mm	600mm	Single Point Locking	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-013	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-014	47U	2200mm	800mm	Single Point Locking	1	Black Grey
21630-015	52U	2450mm	800mm	Single Point Locking	1	Black Grey
21630-408	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-409	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-410	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-411	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-412	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-413	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-414	38U	1800mm	600mm	Single Point Locking	1	Black Grey
21630-415	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-507	24U	1200mm	600mm	Single Point Locking	1	Black Grey
21630-508	24U	1200mm	800mm	Single Point Locking	1	Black Grey
21630-509	29U	1400mm	600mm	Single Point Locking	1	Black Grey
21630-510	29U	1400mm	800mm	Single Point Locking	1	Black Grey
21630-511	33U	1600mm	600mm	Single Point Locking	1	Black Grey
21630-512	33U	1600mm	800mm	Single Point Locking	1	Black Grey
21630-513	38U	1800mm	600mm	Single Point Locking	1	Black Grey

CatalogNumber	Rack Height	Height	Width	Locking Type	Package Quantity	Color
21630-514	38U	1800mm	800mm	Single Point Locking	1	Black Grey
21630-515	42U	2000mm	600mm	Single Point Locking	1	Black Grey
21630-516	42U	2000mm	800mm	Single Point Locking	1	Black Grey
21630-517	47U	2200mm	600mm	Single Point Locking	1	Black Grey
21630-518	47U	2200mm	800mm	Single Point Locking	1	Black Grey

Table 2/2

Catalog Number	Color Code	Complies With	Type	Works With
21630-006	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-007	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-008	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-013	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-014	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-015	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-408	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-409	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-410	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-411	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-412	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-413	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP

Catalog Number	Color Code	Complies With	Type	Works With
21630-414	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-415	RAL 7021	IEC 61587-1, IEC 61587-3	Steel Door, Perforated	Varistar CP
21630-507	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-508	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-509	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-510	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-511	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-512	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-513	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-514	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-515	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-516	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-517	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP
21630-518	RAL 7021	IEC 61587-1	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.