


Horizontal Rail, Front, Type L-KD, Light, Short Lip, 84 HP

Power Utilities

CATALOG NUMBER

34560-184



Combinations of horizontal rails and side panels

	Standard rail	Standard rail with short lip (L-KD)	Standard rail with short lip (L-KD) and side panel	Standard rail with short lip (L-KD) and side panel with short lip
Standard rail	-	+	+	+
Standard rail with short lip (L-KD)	+	+	+	+
Standard rail with short lip (L-KD) and side panel	+	+	+	+
Standard rail with short lip (L-KD) and side panel with short lip	+	+	+	+

Legend: + = can be combined, - = combination not recommended

The horizontal rail with a short lip makes a clean design to the assembled front panel.

CERTIFICATIONS



FEATURES

Standard rail at the front

Installation at top and bottom

Short lip (L-KD)

< 28 HP not to print

Aluminum extrusion, anodized finish, conductive contact surface

PRODUCT ATTRIBUTES

Product Type: Horizontal Rail

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Type: Light, KD

Rack Width: 84 HP

Length: 431.8 mm

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE