

MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

CERTIFICATIONS



FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFICATIONS

Table 1/2						
Catalog Number	Rack Height	Depth	Usable Width	Mounting	Complies With	EMC Shielding
20860-621	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-622	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-624	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-625	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-626	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-627	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-628	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-629	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-630	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-632	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-633	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-634	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-635	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2				
Catalog Number	Product Family	Product Type	Type	Certifications
20860-621	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-622	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-624	MultipacPRO	Subrack/Chassis	Perforated	

Catalog Number	Product Family	Product Type	Type	Certifications
20860-625	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-626	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-627	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-628	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-629	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-630	MultipacPRO	Subrack/Chassis	Perforated	
20860-632	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-633	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-634	MultipacPRO	Subrack/Chassis	Perforated	RoHS
20860-635	MultipacPRO	Subrack/Chassis	Perforated	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE