

NGC-30 Series, Current Sensing Board

nVent RAYCHEM NGC-30 Series - Current Sensing Board is a card rack board module that provides current sensing (ground-fault and line).



FEATURES

Easy to install

Mounted in the NGC-30 panel

SPECIFICATIONS

Voltage Rating: 12 V
Voltage Rating Type: DC
Operating Temperature: -40 to 60 °C

Table 1/1

Catalog Number	Item Name	Height	Width	Depth
10720-002	NGC-30-CTM	89.9 mm	248 mm	35 mm
10720-010	NGC-30-CTM-E	89.9 mm	248 mm	89.9 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT