


# RMM2 Remote Digital Input



nVent RAYCHEM RMM2-DI is a remote monitoring module for digital inputs, providing the capability for the nVent RAYCHEM NGC controllers to read the status of devices remotely and link them back to the electrical heat tracing circuits.

## FEATURES

Simple to install, program and operate

DIN rail mounted, wide range of configurations

Reliable long life

## SPECIFICATIONS

**Input Type:** Digital

Table 1/1

| Catalog Number | Item Name         | Area Classification | Height | Width  | Depth | Input Quantity |
|----------------|-------------------|---------------------|--------|--------|-------|----------------|
| 1244-018083    | RMM2-DI           | Hazardous           | 75 mm  | 125 mm | 60 mm | 15             |
| 1244-018858    | RMM2-DI-8GL-EX-E  | Hazardous           | 160 mm | 260 mm | 91 mm | 15             |
| 1244-018859    | RMM2-DI-15GL-EX-E | Hazardous           | 160 mm | 360 mm | 91 mm | 15             |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM   PYROTENAX   TRACER   NUHEAT**