

# Monitor, Keyboard, Touchpad, 1 U Drawer, Reduced Depth



Designed for standard 19" rackmount designed for comfort  
robust design for heavy use or harsh environment operation

## CERTIFICATIONS



## FEATURES

Pull-out 17" TFT color monitor chassis, 1 U (resolution Full HD; connects to VGA or DVI-D interface)

Keyboard with different keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 450 ... 640 mm

With DVI connection

## SPECIFICATIONS

**Depth:** 400mm  
**Product Type:** Cabinet/Rack Drawer

Table 1/2

| Catalog Number | Rack Height | Color | Color Code | Type | Works With | Keyboard Type |
|----------------|-------------|-------|------------|------|------------|---------------|
|----------------|-------------|-------|------------|------|------------|---------------|

|           |    |           |          |                                   |              |           |
|-----------|----|-----------|----------|-----------------------------------|--------------|-----------|
| 60118-583 | 1U | Jet Black | RAL 9005 | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets | QWERTY UK |
| 60118-584 | 1U | Jet Black | RAL 9005 | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets | QWERTZ    |
| 60118-585 | 1U | Jet Black | RAL 9005 | Monitor,<br>Keyboard,<br>Touchpad | 19" Cabinets | AZERTY    |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 60118-583      | No         |
| 60118-584      | No         |
| 60118-585      | No         |

## ADDITIONAL PRODUCT DETAILS

Further versions on request – With trackball or numeric pad.

Other Keyboard layouts see user manual.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**