

Telescopic Slides C-Profile for Cabinet



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

CERTIFICATIONS



FEATURES

For mounting 84 HP wide sub racks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the sub rack (it is inserted into the guiding profile like a telescopic slide)

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized
Type:	C Profile
Product Type:	Telescopic Slide

Table 1/1

Catalog Number	Depth	Package Quantity	Quick Ship
24562-446	250mm	2	No

Catalog Number	Depth	Package Quantity	Quick Ship
24562-449	600mm	2	No
24562-451	800mm	2	No
24562-452	900mm	2	No
24562-473	1200mm	2	No
24562-474	800mm	2	No
24562-460	500mm	2	No
24562-461	600mm	2	No
24562-464	600mm	2	No
24562-466	800mm	2	No
24562-467	900mm	2	No
24562-468	1000mm	2	No
24562-472	1100mm	2	No

ADDITIONAL PRODUCT DETAILS

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE