

# nVent CADDY Speed Link Catenary Kit



## FEATURES

Kit includes precut length of fuse-cut cable to avoid fraying, pre-assembled hook end fitting and tool-free locking device to save installation time

Fastens to the building structure by looping around and hooking to wire rope

Hook end-fitting easily attaches to eye nut

Spring latch helps provide secure connection

## SPECIFICATIONS

**Wire Rope Diameter:** 6 mm  
**Finish:** Electrogalvanized; Hot-Dip Galvanized  
**Material:** Steel; Zinc Alloy; Polypropylene

Table 1/2

| Catalog Number | Article Number | Wire Rope Length | A     | B     | C     | Height (H) |
|----------------|----------------|------------------|-------|-------|-------|------------|
| SLK6L25        | 196804         | 25m              | 75 mm | 40 mm | 15 mm | 108 mm     |
| SLK6L50        | 196807         | 50m              | 75 mm | 40 mm | 15 mm | 108 mm     |
| SLK6L20        | 196803         | 20m              | 75 mm | 40 mm | 15 mm | 108 mm     |
| SLK6L5         | 196800         | 5m               | 75 mm | 40 mm | 15 mm | 108 mm     |

| CatalogNumber | Article Number | Wire Rope Length | A     | B     | C     | Height (H) |
|---------------|----------------|------------------|-------|-------|-------|------------|
| SLK6L30       | 196805         | 30m              | 75 mm | 40 mm | 15 mm | 108 mm     |
| SLK6L15       | 196802         | 15m              | 75 mm | 40 mm | 15 mm | 108 mm     |
| SLK6L40       | 196806         | 40m              | 75 mm | 40 mm | 15 mm | 108 mm     |
| SLK6L10       | 196801         | 10m              | 75 mm | 40 mm | 15 mm | 108 mm     |

Table 2/2

| Catalog Number | Article Number | Width (W) | Thickness (T) | Angle (a) |
|----------------|----------------|-----------|---------------|-----------|
| SLK6L25        | 196804         | 41 mm     | 30 mm         | 60 ° Max  |
| SLK6L50        | 196807         | 41 mm     | 30 mm         | 60 ° Max  |
| SLK6L20        | 196803         | 41 mm     | 30 mm         | 60 ° Max  |
| SLK6L5         | 196800         | 41 mm     | 30 mm         | 60 ° Max  |
| SLK6L30        | 196805         | 41 mm     | 30 mm         | 60 ° Max  |
| SLK6L15        | 196802         | 41 mm     | 30 mm         | 60 ° Max  |
| SLK6L40        | 196806         | 41 mm     | 30 mm         | 60 ° Max  |
| SLK6L10        | 196801         | 41 mm     | 30 mm         | 60 ° Max  |

## ADDITIONAL PRODUCT DETAILS

Wire Rope Length is measured from the end of the wire rope to the hook side of the swage.

Static load 1 represents a point load in the center of the catenary installation. Static load 2 represents a two or three point distributed load on the catenary installation. Static load 3 represents a four or more point distributed load on the catenary installation.

Preload of the wire rope must be applied using Catenary Tensioning Tool.



#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

