


Non-Insulated Solid Conductor



FEATURES

Solid cable for a variety of applications

Available in smaller spool sizes for convenience

LPA and LPC parts are used for lightning protection system downconductor or grounding applications

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Conductor Size	Cross Section	Diameter (Ø)
ASC0850	711530	Aluminum	Bare	8 mm Solid	50.3mm ²	8 mm
RSCC8100	197860	Steel	Hot-Dip Galvanized	1/0 Solid	50.3mm ²	8 mm
RSCC2SS830	197685	Stainless Steel 304 (EN 1.4301)	Bare	1/0 Solid	50.3mm ²	8 mm
RC-ET-8	198210	Copper	Tinned	1/0 Solid	50.2mm ²	8 mm
RC-EC-8	198160	Copper	Bare	1/0 Solid	50.2mm ²	8 mm

Table 2/2

Catalog Number	Article Number	Length (L)	Unit Weight	Complies With
----------------	----------------	------------	-------------	---------------


ASC0850	711530	50m	0.14 kg	
RSCC8100	197860	125m	0.4 kg	
RSCC2SS830	197685	30m	0.4 kg	
RC-ET-8	198210	100m	0.45 kg	
RC-EC-8	198160	100m	0.45 kg	IEC® EN 62561-2

ADDITIONAL PRODUCT DETAILS

Unit weight is per foot (0.3048 m).

Cut-to-order (CTO) lengths are available for an additional charge.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE