

# Transposition Sections Lay-in Hinged-Cover



Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature.

## INDUSTRY STANDARDS

---

Certified by Canadian Standards Association.

## FEATURES

---

Lay-in Hinged-Cover Transposition Sections are used when it is necessary to rotate the open side of the wireway run by 90 degrees and still retain the lay-in feature

## SPECIFICATIONS

|                    |                           |
|--------------------|---------------------------|
| <b>Color Code:</b> | ANSI 61                   |
| <b>Finish:</b>     | Galvanized; Powder Coated |
| <b>Color:</b>      | Gray                      |
| <b>Material:</b>   | Mild Steel                |

Table 1/1

| Catalog Number | Type                  | Height | Width | Thickness | Sealing Plate Quantity | Sealing Plate Type |
|----------------|-----------------------|--------|-------|-----------|------------------------|--------------------|
| F22LE9KOKT     | Transposition Section | 64mm   | 64mm  | 1.9mm     | 1                      | Flat               |
| F22LE9KT       | Transposition Section | 64mm   | 64mm  | 1.9mm     | 1                      | Flat               |
| F22LKOKT       | Transposition Section | 64mm   | 64mm  | 1.9mm     | 1                      | Flat               |
| F22LKT         | Transposition Section | 64mm   | 64mm  | 1.9mm     | 1                      | Flat               |
| F44LE9KOKT     | Transposition Section | 102mm  | 102mm | 1.9mm     | 1                      | Flat               |
| F44LE9KT       | Transposition Section | 102mm  | 102mm | 1.9mm     | 1                      | Flat               |
| F44LKOKT       | Transposition Section | 102mm  | 102mm | 1.9mm     | 1                      | Flat               |
| F44LKT         | Transposition Section | 102mm  | 102mm | 1.9mm     | 1                      | Flat               |
| F66LE9KOKT     | Transposition Section | 152mm  | 152mm | 1.9mm     | 1                      | Flat               |
| F66LE9KT       | Transposition Section | 152mm  | 152mm | 1.9mm     | 1                      | Flat               |
| F66LKOKT       | Transposition Section | 152mm  | 152mm | 1.9mm     | 1                      | Flat               |
| F66LKT         | Transposition Section | 152mm  | 152mm | 1.9mm     | 1                      | Flat               |
| F88LE9KOKT     | Transposition Section | 203mm  | 203mm | 1.9mm     | 1                      | Flat               |
| F88LE9KT       | Transposition Section | 203mm  | 203mm | 1.9mm     | 1                      | Flat               |

## ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**