

TM20 Mechanical Thermostat



nVent RAYCHEM T-M-20-S is a surface sensing thermostat providing temperature control and temperature limiter in safe areas. Available in 3 temperature ranges. 0-100 °C; 0-200 °C; 50-300 °C.

FEATURES

Easy to use: temperature set point adjustment and limiter reset without opening the enclosure, via removable plugs in the lid

Direct connection of the heating cable

Enclosure protection: both 2 meter long stainless steel fluid filled bulb and capillary are protected at the enclosure by a flexible conduit

High limit cut-out: to prevent the heating system exceeding a preset maximum temperature should the control function fail to operate or an unsafe process temperature occur

SPECIFICATIONS

Hysteresis/Differential: 2.5% of temperature range

Max Voltage: 230 V

Controller Switching Capacity:Max 16 A @ 230 VACLimiter Switching Capacity:Max 16 A @ 230 VACThermostat Type:Mechanical Thermostat

Table 1/1			
Catalog Number	Item Name	Controller Temperature Setting	Limiter Temperature Setting
1244-022644	T-M-20-S/+50+300C	50 - 300 °C	20 - 400 °C
1244-022642	T-M-20-S/0+100C	0 - 100 °C	20 - 150 °C
1244-022643	T-M-20-S/0+200C	0 - 200 °C	130 – 200 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com