

# Varistar CP Base Plate, Multi-Piece



Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

## FEATURES

To cover the base opening

The multi-part base plate is open at the rear (opening to rear 200 mm deep, no rear opening with 300 mm cabinet depth)

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Base

**Material:** Steel

Table 1/2

| Catalog Number | Width | Depth | Package Quantity | Frame      | Color      | Color Code |
|----------------|-------|-------|------------------|------------|------------|------------|
| 21630-616      | 600mm | 600mm | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-617      | 600mm | 800mm | 1                | Stationary | Black Grey | RAL 7021   |

| CatalogNumber | Width | Depth  | Package Quantity | Frame      | Color      | Color Code |
|---------------|-------|--------|------------------|------------|------------|------------|
| 21630-618     | 600mm | 900mm  | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-619     | 600mm | 1000mm | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-620     | 600mm | 1100mm | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-621     | 600mm | 1200mm | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-622     | 800mm | 600mm  | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-623     | 800mm | 800mm  | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-624     | 800mm | 900mm  | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-625     | 800mm | 1000mm | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-626     | 800mm | 1100mm | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-627     | 800mm | 1200mm | 1                | Stationary | Black Grey | RAL 7021   |
| 21630-802     | 600mm | 600mm  | 1                | Mobile     | Black Grey | RAL 7021   |
| 21630-803     | 600mm | 800mm  | 1                | Mobile     | Black Grey | RAL 7021   |
| 21630-804     | 600mm | 900mm  | 1                | Mobile     | Black Grey | RAL 7021   |
| 21630-805     | 600mm | 1000mm | 1                | Mobile     | Black Grey | RAL 7021   |
| 21630-806     | 600mm | 1100mm | 1                | Mobile     | Black Grey | RAL 7021   |
| 21630-807     | 600mm | 1200mm | 1                | Mobile     | Black Grey | RAL 7021   |
| 21630-808     | 800mm | 600mm  | 1                | Mobile     | Black Grey | RAL 7021   |
| 21630-809     | 800mm | 800mm  | 1                | Mobile     | Black Grey | RAL 7021   |

| CatalogNumber | Width | Depth  | Package Quantity | Frame  | Color      | Color Code |
|---------------|-------|--------|------------------|--------|------------|------------|
| 21630-810     | 800mm | 900mm  | 1                | Mobile | Black Grey | RAL 7021   |
| 21630-811     | 800mm | 1000mm | 1                | Mobile | Black Grey | RAL 7021   |
| 21630-812     | 800mm | 1100mm | 1                | Mobile | Black Grey | RAL 7021   |
| 21630-813     | 800mm | 1200mm | 1                | Mobile | Black Grey | RAL 7021   |

| Table 2/2      |               |            |
|----------------|---------------|------------|
| Catalog Number | Finish        | Quick Ship |
| 21630-616      | Powder Coated | No         |
| 21630-617      | Powder Coated | No         |
| 21630-618      | Powder Coated | No         |
| 21630-619      | Powder Coated | No         |
| 21630-620      | Powder Coated | No         |
| 21630-621      | Powder Coated | No         |
| 21630-622      | Powder Coated | No         |
| 21630-623      | Powder Coated | No         |
| 21630-624      | Powder Coated | No         |
| 21630-625      | Powder Coated | No         |
| 21630-626      | Powder Coated | No         |
| 21630-627      | Powder Coated | No         |
| 21630-802      | Powder Coated | No         |

| Catalog Number | Finish        | Quick Ship |
|----------------|---------------|------------|
| 21630-803      | Powder Coated | No         |
| 21630-804      | Powder Coated | No         |
| 21630-805      | Powder Coated | No         |
| 21630-806      | Powder Coated | No         |
| 21630-807      | Powder Coated | No         |
| 21630-808      | Powder Coated | No         |
| 21630-809      | Powder Coated | No         |
| 21630-810      | Powder Coated | No         |
| 21630-811      | Powder Coated | No         |
| 21630-812      | Powder Coated | No         |
| 21630-813      | Powder Coated | No         |

## ADDITIONAL PRODUCT DETAILS

Multi piece base plate is assembled from inside.

Please order grounding, cover plate, brush strip or filter mat separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**