

# Elbow 45-Degree Lay-in Hinged-Cover



Lay-in Hinged-Cover 45-Degree Elbows are used for continuous wireway runs with 45-degree turns. Because sections of lay-in wireway can be mounted with covers oriented in any direction, three different 45-degree elbows are available. Proper selection allows the user to maintain the same access and thereby preserve the lay-in feature for right-angle installations.

## INDUSTRY STANDARDS

---

Certified by Canadian Standards Association.

## FEATURES

---

Lay-in Hinged-Cover 45-Degree Elbows are used for continuous wireway runs with 45-degree turns

Because sections of lay-in wireway can be mounted with covers oriented in any direction, three different 45-degree elbows are available

Proper selection allows the user to maintain the same access and thereby preserve the lay-in feature for right-angle installations

## SPECIFICATIONS

|                    |                           |
|--------------------|---------------------------|
| <b>Color Code:</b> | ANSI 61                   |
| <b>Finish:</b>     | Galvanized; Powder Coated |
| <b>Color:</b>      | Gray                      |
| <b>Material:</b>   | Mild Steel                |

Table 1/1

| Catalog Number | Article Number | Type  | Height | Width | Thickness | Sealing Plate Type |
|----------------|----------------|-------|--------|-------|-----------|--------------------|
| F126LE45A      | 18840          | Elbow | 305mm  | 152mm | 1.9mm     | Flat               |
| F22LE45A       | 18140          | Elbow | 64mm   | 64mm  | 1.9mm     | Flat               |
| F22LE45B       | 18150          | Elbow | 64mm   | 64mm  | 1.9mm     | Flat               |
| F22LE45C       | 18160          | Elbow | 64mm   | 64mm  | 1.9mm     | Flat               |
| F44LE45A       | 18370          | Elbow | 102mm  | 102mm | 1.9mm     | Flat               |
| F44LE45B       | 18380          | Elbow | 102mm  | 102mm | 1.9mm     | Flat               |
| F44LE45C       | 18390          | Elbow | 102mm  | 102mm | 1.9mm     | Flat               |
| F66LE45A       | 18610          | Elbow | 152mm  | 152mm | 1.9mm     | Flat               |
| F66LE45B       | 18620          | Elbow | 152mm  | 152mm | 1.9mm     | Flat               |
| F66LE45C       | 18630          | Elbow | 152mm  | 152mm | 1.9mm     | Flat               |
| F88LE45A       | 19260          | Elbow | 203mm  | 203mm | 1.9mm     | Flat               |
| F88LE45B       | 19270          | Elbow | 203mm  | 203mm | 1.9mm     | Flat               |
| F88LE45C       | 19280          | Elbow | 203mm  | 203mm | 1.9mm     | Flat               |

## ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**