

Industrial Oil MiniChiller, TCO



Industrial Oil Chillers provide precision and reliability in a robust modular design. The high cooling precision enhances production quality, leading to more consistent and superior outcomes. The large range of accessories and options allows multiple chiller configurations, including indoor and outdoor installation for maximum location flexibility. The Industrial Chiller has an eco-friendly design with high performance components.

CERTIFICATIONS



FEATURES

Hermetic compressor.

Refrigeration circuit brass pipes.

Welded brazed stainless plate evaporator.

High-efficiency condensing coil.

Axial fan.

SPECIFICATIONS

Table 1/1						
Catalog Number	Nominal Capacity Watts @50Hz	Nominal Capacity Watts @60Hz	Fluid Type	Nominal Voltage	Rated Frequency	Refrigerant
TC008	900W	1100W	Oil	230V	50 – 60Hz	R134a
TC012	1600W	1900W	Oil	230V	50 – 60Hz	R134a
TC019	2200W	2550W	Oil	230V	50 – 60Hz	R134a
TC031	3000W	3450W	Oil	230V	50 – 60Hz	R134a
TC041	3900W	4450W	Oil	230V	50 – 60Hz	R134a

ADDITIONAL PRODUCT DETAILS

Note: Items are customizable, contact nVent to configure

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE