

# SBS-R-FP Control Panel for Pipe Freeze Protection



## SPECIFICATIONS

|                                 |                                            |
|---------------------------------|--------------------------------------------|
| <b>Phase Quantity:</b>          | 3                                          |
| <b>IP Rating:</b>               | IP65                                       |
| <b>Protection:</b>              | Miniature- / Earth Leakage Circuit Breaker |
| <b>Mounting:</b>                | Wall Mounted                               |
| <b>Over Voltage Protection:</b> | Yes                                        |

Table 1/2

| Catalog Number | Item Name      | Group Quantity | Circuit Breaker Quantity | Circuit Breaker | Main Switch Current Rating | Circuit Breaker Quantity, 30 mA |
|----------------|----------------|----------------|--------------------------|-----------------|----------------------------|---------------------------------|
| 1244-016626    | SBS-R-FP-1X16A | 1              | 1                        | 16 A, Type C    | 40 A                       | 1                               |
| 1244-016627    | SBS-R-FP-3X16A | 1              | 3                        | 16 A, Type C    | 40 A                       | 1                               |
| 1244-016629    | SBS-R-FP-1X10A | 1              | 1                        | 10 A, Type C    | 40 A                       | 1                               |
| 1244-016630    | SBS-R-FP-3X10A | 1              | 3                        | 10 A, Type C    | 40 A                       | 1                               |
| 1244-016628    | SBS-R-FP-6X16A | 2              | 6                        | 16 A, Type C    | 40 A                       | 2                               |
| 1244-016631    | SBS-R-FP-6X10A | 2              | 6                        | 10 A, Type C    | 40 A                       | 2                               |

Table 2/2

| Catalog Number | Item Name      | Height | Width  | Depth  | Housing Material |
|----------------|----------------|--------|--------|--------|------------------|
| 1244-016626    | SBS-R-FP-1X16A | 286 mm | 418 mm | 148 mm | Plastic          |
| 1244-016627    | SBS-R-FP-3X16A | 436 mm | 418 mm | 148 mm | Plastic          |
| 1244-016629    | SBS-R-FP-1X10A | 246 mm | 310 mm | 148 mm | Plastic          |
| 1244-016630    | SBS-R-FP-3X10A | 436 mm | 418 mm | 148 mm | Plastic          |
| 1244-016628    | SBS-R-FP-6X16A | 586 mm | 418 mm | 148 mm | Plastic          |
| 1244-016631    | SBS-R-FP-6X10A | 586 mm | 418 mm | 148 mm | Plastic          |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

Tel +1.800.545.6258  
 Fax +1.800.527.5703  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Europe, Middle East, Africa

Tel +32.16.213.511  
 Fax +32.16.213.604  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### Asia Pacific

Tel +86.21.2412.1688  
 Fax +86.21.5426.3167  
[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### Latin America

Tel +1.713.868.4800  
 Fax +1.713.868.2333  
[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**