nVent | SCHROFF

We connect and protect

VPX System, Rugged, 10 U, 10 Slot, Pluggable PSU

CATALOG NUMBER

20836-780



Rugged VPX system for 10 VPX boards 6 U, 1", 160 mm and 10 Rear I/O boards. The power for the system is supplied by a pluggable VPX power supply. A fan control module monitors the fans, the temperature and voltage.

FEATURES

- System designed in accordance with: MIL-STD-810F, MIL-STD-167, MIL-STD-461, IP 20
- For rugged applications with increased shock and vibration resistance
- PSU, 1 pluggable power supply, 1000 W, 6 U, space for a second PSU
- Backplane VPX 10 slot, 6 U, in accordance with VITA 65, Backplane Profile BKP6-CEN10-11.2.4.4
- 100 to 240 VAC input on the back, main switch on the front of the chassis
- LED voltage and fan fail indicator on the front
- 6 U Front card cage and 6U Rear I/O card cage, with 10 Slot VPX backplane
- Prepared for Telescopic slides
- Optimal EMC protection through hinged front and rear panel with integrated Honeycomp filter

PRODUCT ATTRIBUTES

- Product Type: System
- Number of Slots: 10
- Type: Rugged 19" Rack Mount
- Backplane Type: VPX, VITA 65
- Data Transfer: 10 GbE; PCIe Gen3

Power per Slot: 50W

Input Voltage AC: 100 – 240V

Airflow Direction: Front to Rear

Rack Height: 10U

Power Supply Type: (1) Pluggable PSU

Power Supply Included: Yes

Rear I/O: Yes

Complies With: ANSI/VITA 46.0-2019

Power: 1000W

Depth: 490mm

Height: 443.7mm

Width: 480mm

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Modified systems available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.