

Varistar CP EMC Cabinet, IP 55



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

Shielding 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3)

Shielding 30 dB at 18 GHz, (tested to EN 61000-5-7) with EN45545 gaskets

Type of protection IP 55

Static load-carrying capacity 1600 kg

Doors with 4-point locking and screw-fixed side panels

Side and rear panels can be installed by one person

SPECIFICATIONS

Static Load: 1600kg
Product Type: Cabinet
Protection Rating: IP55
Cladding Color Code: RAL 7021
Frame Material: Steel

Table 1/3						
Catalog Number	Rack Height	Height	Frame Color	Width	Frame Color Code	Cable Entry
10630-044	42U	2000mm	Black Grey	600mm	RAL 7021	Yes
10630-043	42U	2000mm	Black Grey	600mm	RAL 7021	No

Table 2/3						
Catalog Number	Cladding Material	Depth	Cladding Color	Package Quantity	Complies With	Finish
10630-044	Steel	800mm	Black Grey	1	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Powder Coated
10630-043	Steel	800mm	Black Grey	1	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Powder Coated

Table 3/3					
Catalog Number	Material	Quick Ship			
10630-044	Steel	No			
10630-043	Steel	No			

ADDITIONAL PRODUCT DETAILS

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America	
All locations	
+1.763.422.2661	
Chat with us:	

nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us:

nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE