

NM Cable to Rod/Wire Clip



CERTIFICATIONS



FEATURES

Supports non-metallic sheathed cable with ground wire

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Flange Thickness	Outer Diameter	Rod Size
RMX4Z34	171096	Spring Steel	nVent CADDY Armour	3.9 - 9.5 mm	7 - 8 mm	4, 6, 8, 10

Table 2/2

Catalog Number	Article Number	Wire Size
RMX4Z34	171096	3.9 - 4.8 mm

ADDITIONAL PRODUCT DETAILS

Assemblies allow support from most main and substructures.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

