

# TRC Four Pole Distribution Block, 400 A

## Data Solutions



### CERTIFICATIONS



### FEATURES

Transparent protection cover

Bolts included for output connections

Easy accessibility for wiring

Ready to use out of the box, saving installation time and labor

RoHS compliant

### SPECIFICATIONS

Catalog Number	TRC-400A
Article Number	563180
Material	Copper Glass Fibre Reinforced Polyamide Plexiglass
Max Working Voltage, IEC (Ui)	1000


Catalog Number	TRC-400A
Peak Short Circuit Current (I <sub>pk</sub> )	118kA
Short Term Withstand Current (I <sub>cw</sub> ) 1s	28kA
Line Side Number of Connections	1
Load Side Number of Connections	10
Thread Size 1 (TS1)	M6
Thread Size 2 (TS2)	M10
Depth (D)	50mm
Height (H)	338 – 390mm
Width (W)	260mm
A	290mm
Unit Weight	2.65kg
Flammability Rating	UL® 94V-0
Complies With	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C)

## ADDITIONAL PRODUCT DETAILS

Thread Size 2 represents input plug.

Line side and load side number of connections are per pole.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**