

# Varistar CP Glazed Door With 3-Point Locking

## Data Solutions



Glazed door with 3 point locking allows stronger contact between door and the cabinet frame.

### FEATURES

Glazed Door With 3-Point Locking, With Lock

Lever handle with key insert (2 keys)

Opening angle 180°

Security glass, 6 mm

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

### SPECIFICATIONS

**Locking Type:** 3-Point Locking

**Product Type:** Cabinet Door

**Material:** Steel; Glass

Table 1/2

| Catalog Number | Rack Height | Height | Width | Protection Rating | Package Quantity | Color      |
|----------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-095      | 42U         | 2000mm | 800mm | IP20              | 1                | Black Grey |
| 21630-093      | 47U         | 2200mm | 600mm | IP20              | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-725     | 42U         | 2000mm | 600mm | IP55              | 1                | Black Grey |
| 21630-420     | 33U         | 1600mm | 600mm | IP20              | 1                | Black Grey |
| 21630-417     | 24U         | 1200mm | 800mm | IP20              | 1                | Black Grey |
| 21630-724     | 38U         | 1800mm | 800mm | IP55              | 1                | Black Grey |
| 21630-094     | 52U         | 2450mm | 600mm | IP20              | 1                | Black Grey |
| 21630-723     | 38U         | 1800mm | 600mm | IP55              | 1                | Black Grey |
| 21630-421     | 33U         | 1600mm | 800mm | IP20              | 1                | Black Grey |
| 21630-722     | 33U         | 1600mm | 800mm | IP55              | 1                | Black Grey |
| 21630-422     | 38U         | 1800mm | 600mm | IP20              | 1                | Black Grey |
| 21630-418     | 29U         | 1400mm | 600mm | IP20              | 1                | Black Grey |
| 21630-721     | 33U         | 1600mm | 600mm | IP55              | 1                | Black Grey |
| 21630-416     | 24U         | 1200mm | 600mm | IP20              | 1                | Black Grey |
| 21630-720     | 29U         | 1400mm | 800mm | IP55              | 1                | Black Grey |
| 21630-096     | 47U         | 2200mm | 800mm | IP20              | 1                | Black Grey |
| 21630-719     | 29U         | 1400mm | 600mm | IP55              | 1                | Black Grey |
| 21630-423     | 38U         | 1800mm | 800mm | IP20              | 1                | Black Grey |
| 21630-718     | 24U         | 1200mm | 800mm | IP55              | 1                | Black Grey |
| 21630-717     | 24U         | 1200mm | 600mm | IP55              | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Protection Rating | Package Quantity | Color      |
|---------------|-------------|--------|-------|-------------------|------------------|------------|
| 21630-097     | 52U         | 2450mm | 800mm | IP20              | 1                | Black Grey |
| 21630-727     | 47U         | 2200mm | 600mm | IP55              | 1                | Black Grey |
| 21630-726     | 42U         | 2000mm | 800mm | IP55              | 1                | Black Grey |
| 21630-419     | 29U         | 1400mm | 800mm | IP20              | 1                | Black Grey |
| 21630-092     | 42U         | 2000mm | 600mm | IP20              | 1                | Black Grey |
| 21630-728     | 47U         | 2200mm | 800mm | IP55              | 1                | Black Grey |

Table 2/2

| Catalog Number | Color Code | Complies With            | Finish        | Type       | Works With  |
|----------------|------------|--------------------------|---------------|------------|-------------|
| 21630-095      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-093      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-725      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-420      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-417      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-724      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-094      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-723      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-421      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-722      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-422      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |

| Catalog Number | Color Code | Complies With            | Finish        | Type       | Works With  |
|----------------|------------|--------------------------|---------------|------------|-------------|
| 21630-418      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-721      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-416      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-720      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-096      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-719      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-423      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-718      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-717      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-097      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-727      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-726      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |
| 21630-419      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-092      | RAL 7021   | IEC 61587-1, IEC 61587-3 | Powder Coated | Glass Door | Varistar CP |
| 21630-728      | RAL 7021   | IEC 61587-1              | Powder Coated | Glass Door | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**