

# Cable to Web of Rail TB5 Complete Welder, Signal



## FEATURES

Complete right hand or left hand web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis of 85 to 141 lb. rail

## SPECIFICATIONS

|                             |                                 |
|-----------------------------|---------------------------------|
| <b>Bond Terminal Style:</b> | 1" Tab                          |
| <b>Rail Type:</b>           | 85 lb to 141 lb T-Rail Sections |
| <b>Material:</b>            | Graphite;Steel;Thermoplastic    |

Table 1/1

| Catalog Number | Conductor Size   | Conductor Outer Diameter, Nominal | Welder Style | Orientation |
|----------------|------------------|-----------------------------------|--------------|-------------|
| SBWRTB5ALH     | 3/16" Bondstrand | 4.76mm                            | TB5          | Left Hand   |
| SBWRTB5ARH     | 3/16" Bondstrand | 4.76mm                            | TB5          | Right Hand  |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**