

Brackets For 19-Inch Partial Height Mounting Profiles, CIC



These brackets, for mounting 19" partial profiles in 800mm wide enclosures, can be adjusted in height and depth.

FEATURES

Description: For fixing 19" vertical profiles CIPP in 800 mm wide enclosures. Adjustable in depth in steps of 25 mm by using the CLPK click-in profiles.

Material: 3 mm zinc plated steel.

Pack quantity: 4 brackets with mounting accessories.

SPECIFICATIONS

Table 1/1						
Catalog Number	Height	Width	Depth	Material	Finish	Thickness
CIC04	49mm	100mm	50mm	Mild Steel	Zinc Plated	3mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE