

# Enclosure Pole Fixation, EPF



This pole fixation kit allows the enclosure to be mounted on a variety of poles at the desired height.

## FEATURES

---

Description: Accessory to fix enclosures onto poles. Maximum load of 900 N.

Material: Galvanized steel.

Minimum pole diameter: 80 mm.

Maximum pole diameter: 250 mm.

Pack quantity: 2 profiles, 2 circular mounting strips for pole attachment and mounting accessories.

## SPECIFICATIONS

**Thickness:** 3mm  
**Finish:** Galvanized  
**Material:** Mild Steel

Table 1/1

| Catalog Number | Height | Width | Depth | Enclosure Material    | Product Family               | Quick Ship |
|----------------|--------|-------|-------|-----------------------|------------------------------|------------|
| EPF0300        | 35mm   | 296mm | 25mm  | Mild Steel, Polyester | Wall Mounted, Terminal Boxes | No         |
| EPF0400        | 35mm   | 396mm | 25mm  | Mild Steel, Polyester | Wall Mounted, Terminal Boxes | No         |
| EPF0600        | 35mm   | 596mm | 25mm  | Mild Steel, Polyester | Wall Mounted, Terminal Boxes | No         |
| EPF0500        | 35mm   | 496mm | 25mm  | Mild Steel, Polyester | Wall Mounted, Terminal Boxes | No         |
| EPF0800        | 35mm   | 796mm | 25mm  | Mild Steel, Polyester | Wall Mounted, Terminal Boxes | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**