

## Side Panels Stainless Steel, SPMS



These side panels will ensure that the ingress protection is maintained, which means that the electrical components will operate without any disturbances and protect personnel from injuries.

### FEATURES

---

Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws and new patented retainers.

Protection: IP 55, TYPE 12, 13 in combination with MCSS. IP66, TYPE 4X, 12 in combination with MCSS-HP.

Pack quantity: 2 panels with mounting accessories.

Material: 1.5 mm AISI 304 / AISI 316L pre-grained stainless steel.

Finish: 400 pre-grained stainless steel.

SPECIFICATIONS

Thickness: 1.5mm  
Finish: Brushed

| Table 1/1      |        |       |       |                     |                |                    |
|----------------|--------|-------|-------|---------------------|----------------|--------------------|
| Catalog Number | Height | Width | Depth | Material            | Product Family | Enclosure Material |
| SPMS2006-316   | 1964mm | 18mm  | 562mm | Stainless Steel 316 | Free-Standing  | Mild Steel         |
| SPMS1805-316   | 1764mm | 18mm  | 462mm | Stainless Steel 316 | Free-Standing  | Mild Steel         |
| SPMS2006       | 1964mm | 18mm  | 562mm | Stainless Steel 304 | Free-Standing  | Mild Steel         |
| SPMS1805       | 1764mm | 18mm  | 462mm | Stainless Steel 304 | Free-Standing  | Mild Steel         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE