

Connection Kit, Cold-Applied



nVent RAYCHEM C25-100 is a cold-applied core sealer kit suitable as power connection for all nVent RAYCHEM self-regulating and power-limiting industrial parallel heating cables.

FEATURES

Simple and fast to install

Cold-applied: core sealing boot with non-curing sealant; no heat gun, no hot work permit needed

One component for all nVent RAYCHEM industrial parallel heating cables

Simplified design in hazardous area, integral part of system approval

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Table 1/1

Catalog Number	Item Name	E-Number	Model	Connection Type	Thread Size	Max Exposure Temperature
263012-000	C25-100	0431174	Connection to Junction Box	Cold Applied	M25	110 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT