

# ETS-05 Electronic Thermostat



nVent RAYCHEM ETS-05 hazardous area electronic surface sensing thermostats provide accurate temperature control for heating cables. The ETS-05 is available as an Ambient sensing thermostat and as line sensing thermostat. The ETS-05-L is adjustable to 199 °C, ETS-05-H up to 499 °C. ETS-05 has a LED to indicate status of the thermostat, heating cable and sensor. The ETS-05 is available with an alarm relay for remote monitoring.

## FEATURES

Simple to install and operate

Temperature set by digital rotary switches inside the enclosure

PT100 sensor supplied with 2m cable

Available with earth plate

Alarm relay optional

## SPECIFICATIONS

|                         |                                |
|-------------------------|--------------------------------|
| <b>Thermostat Type:</b> | Electronic Thermostat          |
| <b>Material:</b>        | Glass Fiber Reinforced Polymer |
| <b>IP Rating:</b>       | IP66                           |

Table 1/2

| Catalog Number | Item Name    | E-Number | Controller Temperature Setting | Max Measuring Range | Height | Width  |
|----------------|--------------|----------|--------------------------------|---------------------|--------|--------|
| 1244-014367    | ETS-05-L2-E  | 2615439  | 0 – 199 °C                     | 260 °C              | 90 mm  | 120 mm |
| 1244-014368    | ETS-05-H2-E  | 2615440  | 0 – 499 °C                     | 585 °C              | 90 mm  | 120 mm |
| 1244-017508    | ETS-05-L2-EP |          | 0 – 199 °C                     | 260 °C              | 90 mm  | 120 mm |
| 1244-017509    | ETS-05-H2-EP |          | 0 – 499 °C                     | 585 °C              | 90 mm  | 120 mm |

| CatalogNumber | Item Name       | E-Number | Controller Temperature Setting | Max Measuring Range | Height | Width  |
|---------------|-----------------|----------|--------------------------------|---------------------|--------|--------|
| 1244-022311   | ETS-05-A2-E     |          | 0 – 49 °C                      | 260 °C              | 90 mm  | 120 mm |
| 1244-022663   | ETS-05-A2-E-A   |          | 0 – 49 °C                      | 260 °C              | 150 mm | 120 mm |
| 1244-022669   | ETS-05-L2-EP-A  |          | 0 – 199 °C                     | 260 °C              | 150 mm | 120 mm |
| 1244-022670   | ETS-05-H2-EP-A  |          | 0 – 499 °C                     | 585 °C              | 150 mm | 120 mm |
| 1244-022680   | ETS-05-H2R-EP-A |          | 0 – 499 °C                     | 585 °C              | 150 mm | 120 mm |
| 1244-022675   | ETS-05-H2R-E-A  |          | 0 – 499 °C                     | 585 °C              | 150 mm | 120 mm |

Table 2/2

| Catalog Number | Item Name       | E-Number | Depth  | Earth Plate Included | Alarm Relay |
|----------------|-----------------|----------|--------|----------------------|-------------|
| 1244-014367    | ETS-05-L2-E     | 2615439  | 120 mm | No                   | No          |
| 1244-014368    | ETS-05-H2-E     | 2615440  | 120 mm | No                   | No          |
| 1244-017508    | ETS-05-L2-EP    |          | 120 mm | Yes                  | No          |
| 1244-017509    | ETS-05-H2-EP    |          | 120 mm | Yes                  | No          |
| 1244-022311    | ETS-05-A2-E     |          | 120 mm | No                   | No          |
| 1244-022663    | ETS-05-A2-E-A   |          | 120 mm | No                   | Yes         |
| 1244-022669    | ETS-05-L2-EP-A  |          | 120 mm | Yes                  | Yes         |
| 1244-022670    | ETS-05-H2-EP-A  |          | 120 mm | Yes                  | Yes         |
| 1244-022680    | ETS-05-H2R-EP-A |          | 120 mm | Yes                  | Yes         |
| 1244-022675    | ETS-05-H2R-E-A  |          | 120 mm | No                   | Yes         |

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Europe, Middle East, Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

### **Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

### **Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**