

MONI-PT100-260 RTD Sensor for Non-Hazardous Areas



SPECIFICATIONS

Max Measuring Range:	260 °C
Mounting:	Pipe Strap
Sensor Type:	PT100
Material:	PTFE
Fixed Cable to Sensor:	Yes

Table 1/1

Catalog Number	Item Name	E-Number	Cable Length
1244-006615	PT100-260/2	2615441	2 m
1244-020816	MONI-PT100-260/10		10 m
1244-020817	MONI-PT100-260/5		50 m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT