

SBS-R-FP Control Panel for Pipe Freeze Protection



SPECIFICATIONS

Phase Quantity:	3
IP Rating:	IP65
Protection:	Miniature- / Earth Leakage Circuit Breaker
Mounting:	Wall Mounted
Over Voltage Protection:	Yes

Table 1/3

Catalog Number	Item Name	E-Number	Group Quantity	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating
1244-016626	SBS-R-FP-1X16A	3418425	1	1	16 A, Type C	40 A
1244-016627	SBS-R-FP-3X16A	3418427	1	3	16 A, Type C	40 A
1244-016629	SBS-R-FP-1X10A	3418424	1	1	10 A, Type C	40 A
1244-016630	SBS-R-FP-3X10A	3418426	1	3	10 A, Type C	40 A
1244-021775	SBS-R-FP-1X13A		1	3	13 A, Type C	40 A
1244-021776	SBS-R-FP-3X13A		1	3	13 A, Type C	40 A

CatalogNumber	Item Name	E-Number	Group Quantity	Circuit Breaker Quantity	Circuit Breaker	Main Switch Current Rating
1244-016628	SBS-R-FP-6X16A	3418429	2	6	16 A, Type C	40 A
1244-016631	SBS-R-FP-6X10A	3418428	2	6	10 A, Type C	40 A
1244-021777	SBS-R-FP-6X13A		2	6	13 A, Type C	40 A

Table 2/3						
Catalog Number	Item Name	E-Number	Circuit Breaker Quantity, 30 mA	Height	Width	Depth
1244-016626	SBS-R-FP-1X16A	3418425	1	286 mm	418 mm	148 mm
1244-016627	SBS-R-FP-3X16A	3418427	1	436 mm	418 mm	148 mm
1244-016629	SBS-R-FP-1X10A	3418424	1	246 mm	310 mm	148 mm
1244-016630	SBS-R-FP-3X10A	3418426	1	436 mm	418 mm	148 mm
1244-021775	SBS-R-FP-1X13A		1	586 mm	310 mm	148 mm
1244-021776	SBS-R-FP-3X13A		1	586 mm	310 mm	148 mm
1244-016628	SBS-R-FP-6X16A	3418429	2	586 mm	418 mm	148 mm
1244-016631	SBS-R-FP-6X10A	3418428	2	586 mm	418 mm	148 mm
1244-021777	SBS-R-FP-6X13A		2	586 mm	600 mm	148 mm

Table 3/3			
Catalog Number	Item Name	E-Number	Housing Material
1244-016626	SBS-R-FP-1X16A	3418425	Plastic
1244-016627	SBS-R-FP-3X16A	3418427	Plastic
1244-016629	SBS-R-FP-1X10A	3418424	Plastic

Catalog Number	Item Name	E-Number	Housing Material
1244-016630	SBS-R-FP-3X10A	3418426	Plastic
1244-021775	SBS-R-FP-1X13A		Plastic
1244-021776	SBS-R-FP-3X13A		Plastic
1244-016628	SBS-R-FP-6X16A	3418429	Plastic
1244-016631	SBS-R-FP-6X10A	3418428	Plastic
1244-021777	SBS-R-FP-6X13A		Plastic

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT