

XL-Trace Low Smoke Zero Halogen Self-Regulating Heating Cable



nVent RAYCHEM XL-Trace self-regulating trace heating cables provide energy efficient and easy to use solutions for pipe freeze protection and flow maintenance in grease waste lines. Developed with low smoke zero halogen (LSZH) materials, to ensure the safest solution for modern building design.

FEATURES

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Simple to design: long circuit lengths to 215 m, for fewer power connections and faster installation

Easy to install: highly flexible cable, cut to length, meter marks, fast RayClic cold connection system

Energy efficient and safe: self-regulating cable, advanced energy saving controls, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible, low smoke zero halogen

Reliable during long life: 10 year product warranty available, UV resistant, colorfast, maintenance free

SPECIFICATIONS

Nominal Thickness:	6.8 mm
Nominal Width:	13.8 mm
Supply Voltage:	220 – 240 V
Min Installation Temperature:	-40 °C
Ground Path Type:	Braid
Outer Jacket Material:	Low Smoke Zero Halogen
Conductor Material:	Nickel-Plated Copper

Table 1/1

Catalog Number	Item Name	E-Number	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Color
----------------	-----------	----------	----------------------------------	--------------------	-------

P000002113	10XL2-ZH	8171811	10 W/m	238 m	Plum
P000002114	15XL2-ZH	8171812	15 W/m	188 m	Green
P000002115	26XL2-ZH	8171813	26 W/m	142 m	Blue
P000002116	31XL2-ZH	8171814	31 W/m	114 m	Purple

ADDITIONAL PRODUCT DETAILS

Circuit Lengths are based on a 20 A C-Type characteristic circuit protection device, Power on at +5 °C.

When selecting the heating circuit length, the maximum switching capacity of the respective controller must be taken into account.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT