

Eurorack Universal Frame



Screw-fixed, frame Al die-cast, uprights Al extrusion.

CERTIFICATIONS



FEATURES

Finish: RAL 7021

Screw-fixed, frame Al die-cast, uprights Al extrusion

Other dimensions available on request

19" plane, depth-adjustable in 25 mm increments, can be assembled with depth members and 19" panel/slide mounts

SPECIFICATIONS

Static Load:	400kg
Material:	Aluminum
Product Type:	Cabinet/Rack Frame

Table 1/2

Catalog Number	Rack Height	Height	Width	Depth	Package Quantity	Color
22117-792	43U	2020mm	600mm	900mm	1	Black Grey
22117-787	38U	1798mm	600mm	900mm	1	Black Grey
22117-791	43U	2020mm	600mm	800mm	1	Black Grey

Table 2/2

Catalog Number	Color Code	Finish	Frame Material	Type	Certifications	Quick Ship
22117-792	RAL 7021	Powder Coated	Aluminum	Universal		No
22117-787	RAL 7021	Powder Coated	Aluminum	Universal	RoHS	No
22117-791	RAL 7021	Powder Coated	Aluminum	Universal	RoHS	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE