


nVent CADDY Macrofix Insulated M8



CERTIFICATIONS



FEATURES

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

SPECIFICATIONS

| | |
|---------------------|-----------------------|
| Finish: | Electrogalvanized |
| Material: | EPDM-SBR Rubber;Steel |
| Temperature: | -50 to 110 °C |

Table 1/2

| Catalog Number | Article Number | Outer Diameter (OD) | NB/DN | Rod Size (RS) | Width (W) | Thickness (T) |
|----------------|----------------|---------------------|-------|---------------|-----------|---------------|
|----------------|----------------|---------------------|-------|---------------|-----------|---------------|


| | | | | | | |
|--------|--------|------------|----|----|-------|---------|
| MFE015 | 586201 | 11 - 15 mm | 8 | M8 | 20 mm | 1 mm |
| MFE019 | 586202 | 15 - 19 mm | 10 | M8 | 20 mm | 1 mm |
| MFE025 | 586203 | 19 - 25 mm | 15 | M8 | 20 mm | 1 mm |
| MFE031 | 586204 | 25 - 31 mm | 20 | M8 | 20 mm | 1 mm |
| MFE037 | 586205 | 31 - 37 mm | 25 | M8 | 20 mm | 1 mm |
| MFE044 | 586206 | 37 - 44 mm | 32 | M8 | 20 mm | 1 mm |
| MFE050 | 586207 | 44 - 50 mm | 40 | M8 | 20 mm | 1.25 mm |
| MFE058 | 586208 | 50 - 58 mm | | M8 | 20 mm | 1.25 mm |
| MFE068 | 586209 | 58 - 68 mm | 50 | M8 | 20 mm | 1.25 mm |

| Table 2/2 | | | | |
|----------------|----------------|---------------------|------------------|-------------|
| Catalog Number | Article Number | Screw Diameter (Sc) | Screw Length (L) | Static Load |
| MFE015 | 586201 | 6 | 17mm | 1000N |
| MFE019 | 586202 | 6 | 17mm | 1000N |
| MFE025 | 586203 | 6 | 22mm | 1000N |
| MFE031 | 586204 | 6 | 22mm | 1000N |
| MFE037 | 586205 | 6 | 22mm | 1000N |
| MFE044 | 586206 | 6 | 27mm | 1000N |
| MFE050 | 586207 | 6 | 27mm | 1500N |
| MFE058 | 586208 | 6 | 27mm | 1500N |
| MFE068 | 586209 | 6 | 32mm | 1500N |

ADDITIONAL PRODUCT DETAILS

Lining is EPDM rubber.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

