

# Front Panel, Retrofit Shielding



Flat front panel. Shieldable with stainless steel EMC gasket.

## CERTIFICATIONS



## FEATURES

For stainless steel EMC gasket

Al, 2.5 mm, front anodized, conductive

## SPECIFICATIONS

|                        |                            |
|------------------------|----------------------------|
| <b>Depth (D):</b>      | 2.5mm                      |
| <b>Material:</b>       | Aluminum                   |
| <b>Accessory Type:</b> | Front panel                |
| <b>Product Type:</b>   | Front Panel                |
| <b>Type:</b>           | Front Panel without Handle |
| <b>EMC Shielding:</b>  | No (Retrofittable)         |

Table 1/3

| Catalog Number | Rack Height | Rack Width | Package Quantity | Mounting       | Gasket Type         | Front Finish |
|----------------|-------------|------------|------------------|----------------|---------------------|--------------|
| 20846-425      | 3U          | 3HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |

| CatalogNumber | Rack Height | Rack Width | Package Quantity | Mounting       | Gasket Type         | Front Finish |
|---------------|-------------|------------|------------------|----------------|---------------------|--------------|
| 30846-865     | 6U          | 2HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-426     | 3U          | 4HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-427     | 3U          | 5HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-428     | 3U          | 6HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-429     | 3U          | 7HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-443     | 6U          | 4HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-430     | 3U          | 8HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-442     | 6U          | 3HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-431     | 3U          | 10HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-444     | 6U          | 5HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-432     | 3U          | 12HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-445     | 6U          | 6HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-433     | 3U          | 14HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-446     | 6U          | 7HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-424     | 3U          | 16HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-447     | 6U          | 8HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-448     | 6U          | 10HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-434     | 3U          | 21HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |

| CatalogNumber | Rack Height | Rack Width | Package Quantity | Mounting       | Gasket Type         | Front Finish |
|---------------|-------------|------------|------------------|----------------|---------------------|--------------|
| 20846-449     | 6U          | 12HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-436     | 3U          | 28HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-450     | 6U          | 14HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-456     | 6U          | 16HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-451     | 6U          | 21HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-437     | 3U          | 42HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 30846-588     | 2U          | 84HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-452     | 6U          | 28HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-438     | 3U          | 63HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 30846-676     | 3U          | 84HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-453     | 6U          | 42HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 30846-683     | 4U          | 84HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 20846-454     | 6U          | 63HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 30846-771     | 6U          | 84HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 30846-859     | 9U          | 84HP       | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |
| 30846-864     | 3U          | 2HP        | 1                | Screw-on Front | Stainless Steel EMC | Anodized     |

Table 2/3

| Catalog Number | Rear Finish | Treated Edges | Complies With | Finish | Height (H) | Width (W) |
|----------------|-------------|---------------|---------------|--------|------------|-----------|
|----------------|-------------|---------------|---------------|--------|------------|-----------|

|           |            |    |                                 |          |         |        |
|-----------|------------|----|---------------------------------|----------|---------|--------|
| 20846-425 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 14.9mm |
| 30846-865 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 9.8mm  |
| 20846-426 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 20mm   |
| 20846-427 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 25mm   |
| 20846-428 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 30.1mm |
| 20846-429 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 35.2mm |
| 20846-443 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 20mm   |
| 20846-430 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 40.3mm |
| 20846-442 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 14.9mm |
| 20846-431 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 50.5mm |
| 20846-444 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 25mm   |
| 20846-432 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 60.6mm |
| 20846-445 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 30.1mm |
| 20846-433 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 70.8mm |
| 20846-446 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 35.2mm |

|           |            |    |                                 |                      |         |         |
|-----------|------------|----|---------------------------------|----------------------|---------|---------|
| 20846-424 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 128.4mm | 80.9mm  |
| 20846-447 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 40.3mm  |
| 20846-448 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 50.5mm  |
| 20846-434 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 128.4mm | 106.3mm |
| 20846-449 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 60.6mm  |
| 20846-436 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 128.4mm | 141.9mm |
| 20846-450 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 70.8mm  |
| 20846-456 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 80.9mm  |
| 20846-451 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 106.3mm |
| 20846-437 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 128.4mm | 213mm   |
| 30846-588 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized, Passivated | 84mm    | 426.4mm |
| 20846-452 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 141.9mm |
| 20846-438 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 128.4mm | 319.7mm |
| 30846-676 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized, Passivated | 128.4mm | 426.4mm |
| 20846-453 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized             | 261.8mm | 213mm   |

|           |            |    |                                 |          |         |         |
|-----------|------------|----|---------------------------------|----------|---------|---------|
| 30846-683 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 172.9mm | 426.4mm |
| 20846-454 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 319.7mm |
| 30846-771 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 261.8mm | 426.4mm |
| 30846-859 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 395.1mm | 426.4mm |
| 30846-864 | Conductive | No | IEC 60297-3-101, IEEE 1101.1/10 | Anodized | 128.4mm | 9.8mm   |

Table 3/3

| Catalog Number | Quick Ship |
|----------------|------------|
| 20846-425      | No         |
| 30846-865      | No         |
| 20846-426      | No         |
| 20846-427      | No         |
| 20846-428      | No         |
| 20846-429      | No         |
| 20846-443      | No         |
| 20846-430      | No         |
| 20846-442      | No         |
| 20846-431      | No         |
| 20846-444      | No         |

| Catalog Number | Quick Ship |
|----------------|------------|
| 20846-432      | No         |
| 20846-445      | No         |
| 20846-433      | No         |
| 20846-446      | No         |
| 20846-424      | No         |
| 20846-447      | No         |
| 20846-448      | No         |
| 20846-434      | No         |
| 20846-449      | No         |
| 20846-436      | No         |
| 20846-450      | No         |
| 20846-456      | No         |
| 20846-451      | No         |
| 20846-437      | No         |
| 30846-588      | No         |
| 20846-452      | No         |
| 20846-438      | No         |
| 30846-676      | No         |



### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**