

# Speedway Cable Ladder Equal Cross



## CERTIFICATIONS



## FEATURES

Creates a four way intersection for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic

## SPECIFICATIONS

**Finish:** Hot-Dip Galvanized

**Material:** Steel

Table 1/2


| Catalog Number | Article Number | Width (W) | A | B | C | D |
|----------------|----------------|-----------|---|---|---|---|
|----------------|----------------|-----------|---|---|---|---|

|                   |        |        |         |        |         |       |
|-------------------|--------|--------|---------|--------|---------|-------|
| CL110X150ECH<br>D | 840800 | 150 mm | 900 mm  | 530 mm | 771 mm  | 80 mm |
| CL110X300ECH<br>D | 840810 | 300 mm | 1050 mm | 530 mm | 983 mm  | 80 mm |
| CL110X450ECH<br>D | 840820 | 450 mm | 1200 mm | 530 mm | 1195 mm | 80 mm |
| CL110X600ECH<br>D | 840830 | 600 mm | 1350 mm | 530 mm | 1407 mm | 80 mm |
| CL110X750ECH<br>D | 840840 | 750 mm | 1500 mm | 530 mm | 1619 mm | 80 mm |
| CL110X900ECH<br>D | 840850 | 900 mm | 1650 mm | 530 mm | 1831 mm | 80 mm |

Table 2/2

| Catalog Number | Article Number | E      |
|----------------|----------------|--------|
| CL110X150ECHD  | 840800         | 110 mm |
| CL110X300ECHD  | 840810         | 110 mm |
| CL110X450ECHD  | 840820         | 110 mm |
| CL110X600ECHD  | 840830         | 110 mm |
| CL110X750ECHD  | 840840         | 110 mm |
| CL110X900ECHD  | 840850         | 110 mm |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

