We connect and protect

Varistar CP 19" Panel/Slide Mount, RAL 9005, 47 U, 2200H

Data Solutions

CATALOG NUMBER

24630-014



Slide mout with adjustable increments. Assembly in 600 mm wide cabinets directly on the frame. At 800 mm width adapter bracket for reduced width is neccessary, for partial-height mounting depth members are necessary.

FEATURES

- 19" panel/slide mount with U indicator
- Depth-adjustable in 25 mm increments
- In accordance with IEC 60297-1 (DIN 41 494, Part 1)

PRODUCT ATTRIBUTES

- Rack Height: 47U
- Height: 2200mm
- Package Quantity: 4
- Color: Jet Black
- Color Code: RAL 9005
- Finish: Powder Coated
- Material: Steel
- Product Family: Varistar CP

Product Type: Slide Mount

Net Weight: 19.338kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.