

nVent ERIFLEX Flexbus HCBC Plate with PE Connection

Data Solutions



CERTIFICATIONS



FEATURES

Rigid tinned copper part provides strong electrical contact to maintain braid expansion during compression

HCBC Plate allows Flexbus Conductor insulation to overlap the connection palm

HCBC Plate with PE connection allows conductor to be added to interconnect neutral and ground/earth

Tinned copper allows for copper or aluminum conductor connections

Installs quickly and easily

RoHS compliant

SPECIFICATIONS

Material: Copper

Finish: Tinned

Table 1/2

Catalog Number	Article Number	A	B	C	D	E
FLEXPLATE50PE	508182	65mm	100mm	45mm	41mm	70mm
FLEXPLATE100PE	508183	115mm	100mm	45mm	51mm	70mm

Table 2/2

Catalog Number	Article Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Thickness (T)	Conductor Size	Unit Weight
FLEXPLATE50PE	508182	10.5mm	14.5mm	5mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²	0.49kg
FLEXPLATE100PE	508183	12.5mm	18.5mm	5mm	960 mm ² , 1280 mm ² , 1810 mm ²	0.71kg

ADDITIONAL PRODUCT DETAILS

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE