

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Power Utilities

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FEATURES

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Height	Width	Color	Color Code	Complies With
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Catalog Number	Finish	Locking Type	Material	Product Type	Protection Rating	Type
21630-820	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Powder Coated	3-Point Locking, Electronic	Steel	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Catalog Number	Works With
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE