

19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



FEATURES

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFICATIONS

Product Type: Assembly Kit

Finish: Zinc Plated

Table 1/2

| Catalog Number | Length | Package Quantity | Thread Size | Material | Product Family | Type |
|----------------|--------|------------------|-------------|----------|----------------|------|
|----------------|--------|------------------|-------------|----------|----------------|------|

| | | | | | | |
|-----------|------|-----|----|------------|---|----------------------------|
| 21190-095 | | 4 | M6 | Steel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor | Mounting Kit |
| 21120-196 | 16mm | 4 | M6 | Steel | | Mounting Kit, Grounding |
| 21120-213 | | 4 | M6 | Steel | | Mounting Kit |
| 21100-435 | | 8 | M6 | Steel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |
| 21120-199 | 13mm | 100 | M6 | Steel | | Mounting Kit, Grounding |
| 21120-197 | 16mm | 32 | M6 | Steel | | Mounting Kit, Grounding |
| 21120-198 | 16mm | 50 | M6 | Steel | | Mounting Kit, Grounding |
| 21101-809 | | 50 | M6 | Steel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |

| | | | | | | |
|-----------|--|-----|----|------------|---|--------------|
| 21101-810 | | 100 | M6 | Steel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor | Mounting Kit |
| 21190-435 | | 32 | M6 | Steel, ABS | RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor | Mounting Kit |
| 21120-215 | | 32 | M6 | Steel | | Mounting Kit |
| 21120-214 | | 50 | M6 | Steel | | Mounting Kit |
| 21120-216 | | 100 | M6 | Steel | | Mounting Kit |

Table 2/2

| Catalog Number | Works With | Certifications | Quick Ship |
|----------------|---|----------------|------------|
| 21190-095 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS | No |
| 21120-196 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |
| 21120-213 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |
| 21100-435 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS | No |
| 21120-199 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |

| Catalog Number | Works With | Certifications | Quick Ship |
|----------------|---|----------------|------------|
| 21120-197 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |
| 21120-198 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |
| 21101-809 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS | No |
| 21101-810 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS | No |
| 21190-435 | 19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets | RoHS | No |
| 21120-215 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |
| 21120-214 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |
| 21120-216 | Front Panels, Eurorack, Novastar, Varistar, Varistar CP | | No |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE