

Varistar CP Steel Door, Plain, Multi-Point Locking

EMC and IP55 Steel Door with lever handle and 4-Point locking.

FEATURES

Lever handle with push button

Opening angle 180°

Steel door with 4-point locking for EMC applications

SPECIFICATIONS

Product Type: Cabinet Door
Protection Rating: IP55
Material: Stainless Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Package Quantity	Finish	Locking Type
21630-521	24U	1200mm	600mm	1	Powder Coated	3-Point Locking
21630-522	24U	1200mm	800mm	1	Powder Coated	3-Point Locking
21630-523	29U	1400mm	600mm	1	Powder Coated	3-Point Locking
21630-524	29U	1400mm	800mm	1	Powder Coated	3-Point Locking
21630-525	33U	1600mm	600mm	1	Powder Coated	4-Point Locking
21630-526	33U	1600mm	800mm	1	Powder Coated	4-Point Locking
21630-527	38U	1800mm	600mm	1	Powder Coated	4-Point Locking

CatalogNumber	Rack Height	Height	Width	Package Quantity	Finish	Locking Type
21630-528	38U	1800mm	800mm	1	Powder Coated	4-Point Locking
21630-529	42U	2000mm	600mm	1	Powder Coated	4-Point Locking
21630-530	42U	2000mm	800mm	1	Powder Coated	4-Point Locking
21630-531	47U	2200mm	600mm	1	Powder Coated	5-Point Locking
21630-532	47U	2200mm	800mm	1	Powder Coated	5-Point Locking

Table 2/2

Catalog Number	Quick Ship
21630-521	No
21630-522	No
21630-523	No
21630-524	No
21630-525	No
21630-526	No
21630-527	No
21630-528	No
21630-529	No
21630-530	No
21630-531	No
21630-532	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE