

# VPX System, Desktop, 4 U, 5 Slot, Pluggable PSU



TVPX desktop case for 5 VPX boards 3 U, 160 mm. With or without Rear I/O option The power for the system is supplied by a pluggable open frame power supply.

## CERTIFICATIONS



## FEATURES

Backplane conforms to VITA 46 Other VPX backplanes on request System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with VITA 1.1-1994

PSU pluggable, 300 W, 3 U, 8 HP (further PSU optional)

VPX backplane, in accordance with VITA 46, 5 slot, 3 U, 0.8" pitch, full mesh topology

Heat dissipation by 2 radial fans , front to rear side cooling

## SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
20836-444	System	5	Desktop	VPX Full Mesh	10 GbE	30W
20836-447	System	5	Desktop	VPX Full Mesh	10 GbE	30W

Table 2/3

Catalog Number	Input Voltage AC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
20836-444	100 – 240V	Front to Rear	4U	(1) Pluggable PSU	Yes	No
20836-447	100 – 240V	Front to Rear	4U	(1) Pluggable PSU	Yes	Yes

Table 3/3

Catalog Number	Complies With	Depth	Height	Package Quantity	Quick Ship
20836-444	ANSI/VITA 46.0-2019	275mm	177mm	1	No
20836-447	ANSI/VITA 46.0-2019	275mm	177mm	1	No

## ADDITIONAL PRODUCT DETAILS

Modified systems available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**