

# **C-FIX M T-Bolt**



## **FEATURES**

C-Fix quick fit T-bolt

Suitable for C-Profiles 0-4

## **SPECIFICATIONS**

Finish: Electrogalvanized

Material: Steel


Table 1/1					
<b>Catalog Number</b>	Article Number	Screw Diameter (Sc)	Screw Length (L)	Static Load	
CFIXM8030	584530	8	30mm	300N	
CFIXM8040	584540	8	40mm	300N	
CFIXM8060	584550	8	60mm	300N	


# **ADDITIONAL PRODUCT DETAILS**

Sliding force F2 is limited to 600 N for all types of Nuts and T-Bolts for C-channel System.

Nuts and T-Bolts for C-channel System			
C-Channel Type	Pullout Force F1		
EO	1100 N		
EOL	700 N		
E1	1800 N		
E2	800 N		
E2L	800 N		
E3	1500 N		
E4	1300 N		

#### **DIAGRAMS**





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

# Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

**TRACHTE** 

