

nVent CADDY Quick Clip Rod Stiffener

Data Solutions



FEATURES

Secures strut channel to threaded rod for stiffening

One hand, snap-in place installation

No tools or bolt tightening required


SPECIFICATIONS

Material: Stainless Steel 316 (EN 1.4401)

Table 1/1

Catalog Number	Article Number	Strut Type	Rod Size (RS)
CSBRS2	404538	A (41 x 41 mm)	10
CSBRS3	404539	A (41 x 41 mm)	12
CSBRS4	402532	A (41 x 41 mm)	16

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE